






FOCAL LENGTH (EFL): $-125 \pm 1,25$
 BACK FOCAL LENGTH (BFL): $-128,3$

- 1 VIS-EXT
 $R(\text{AVG}) \leq 0,5\%$ FROM 350 - 700nm @ 0° AOI

LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 64,6 CV			GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL		
Øe 49				Øe 49		
⌀ SEE NOTE 1				⌀ SEE NOTE 1		
3/ 3 (0,5) λ=632,8 nm				3/ 3 (0,5) λ=632,8 nm		
4/ -				4/ 1,93'		
5/ 40 - 20				5/ 40 - 20		
6/ -			6/ -			
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 	 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	50mm Dia x -125mm FL, VIS-EXT Coated, Plano-Concave Lens	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING						
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	26667
			SHEET T SIZE A4			SHEET 1 OF 1