


1550nm TECHSPEC Low GDD Dielectric Ultrafast Laser Mirrors

Coating Specification:

R(avg) S & P >99.90% @ 1550nm @ 45° AOI

R(avg) >99.7% @ 1510 - 1590nm @ 45° AOI

Theoretical Reflection Curve



© COPYRIGHT 2020 EDMUND OPTICS, INC. ALL RIGHTS RESERVED


1550nm TECHSPEC Low GDD Dielectric Ultrafast Laser Mirrors

GDD Specification:

$\pm 20 \text{ fs}^2$ @ 1510 - 1590nm @ 45° AOI (s-pol)

$\pm 30 \text{ fs}^2$ @ 1530 - 1580nm @ 45° AOI (p-pol)

Theoretical GDD Curve



© COPYRIGHT 2020 EDMUND OPTICS, INC. ALL RIGHTS RESERVED