




- NOTES:
- 1. SUBSTRATE: FUSED SILICA
  - 2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN <0.5 ARCMIN
  - 3. COATING (APPLY ACROSS CLEAR APERTURE)
    - S1: Laser V-Coat (532nm)
    - Rabs <0.25% @ 532nm @ 0 ±5° AOI
- DAMAGE THRESHOLD,  
PULSED: 10 J/cm2 @ 532nm, 20ns, 20Hz
- S2: NONE

4. FINE GRIND SURFACE

5. ROHS COMPLIANT




**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	20 - 10	20 - 10
CLEAR APERTURE	90%	90%
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE  
PROJECTION

ALL DIMS INmm

 Edmund Optics®

TITLE

12.7mm Dia., 1mm Thick, 532nm, Nd:YAG  
Laser Line Beam Sampler

DWG NO

29012

SHEET  
3 OF 8