

1. SUBSTRATE:  
FUSED SILICA

2. PARALLELISM: 30 ARCSEC

### 3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: UV Enhanced Aluminum (250-700nm)




R(avg) >85% @ 250 - 700nm

R(avg) >89% @ 250 - 450nm

S2: NONE

#### 4. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE



## 5. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2			 Edmund Optics®		
SHAPE	PLANO	PLANO	<div>THIRD ANGLE PROJECTION</div> 		TITLE	25mm Dia UV Enhanced Aluminum, λ/20 Mirror	
SURFACE QUALITY	20 - 10	COMMERICAL POLISH					
SURFACE FLATNESS	λ/20 (PRE-COATING)	N/A					
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm	DWG NO	70291	SHEET 4 OF 8