

Laser Pulse Parameter Measurement



D200-SI

Features:

- 1. Wavelength range:200-1100nm
- 2. High speed work, rise time 1ns
- 3. Active area diameter: 0.8mm²
- 4. Fiber coupling via SM1 optical adapter

SPECIFICATIONS

Model	D200-SI
Wavelength Range	200-1100nm
Sensitive Area	0.8mm ²
Material	Si
Rise Time	1ns
Bandwidth	350MHz
NEP	5.0x10 ⁻¹⁴ W/Hz ^{1/2}
Dark Current	0.3nA(Typ) 2.5nA(Max)
Warranty period	1 year

D200-SI

