

Laser Pulse Parameter Measurement



D320-SI

- Features:
- 1. Wavelength range:320-1100nm
 - 2. High speed work, rise time 35ns
 - 3. Active area diameter: 75.4mm²
 - 0. Fiber coupling via SM1 optical adapter

SPECIFICATIONS

Model	D320-SI
Wavelength Range	320-1100nm
Sensitive Area	75.4mm ² (Φ9.8mm)
Material	Si
Rise Time	35ns
Bandwidth	10MHz
NEP	2.4x10 ⁻¹⁴ W/Hz ^{1/2}
Dark Current	0.9nA(Typ) 10nA(Max)
Warranty period	1 year

D320-SI

