





f' : $7 \pm 0,07$

BACK FOCAL LENGTH (BFL): 5,5



LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 5,5 CX Øe 6,3 λ AR R(532nm, 0°) < 0,25% R(1064nm, 0°) < 0,25% Rave(500nm - 1100nm, 0°) < 1,00% 3/ 3 (0,5) λ=632,8 nm 4/ 3,82' 5/ 40 - 20 6/ - P			GLASS N-SF11 785/258 Nd: 1,785 Vd: 25,68	R ∞ PL Øe 6,3 λ AR R(532nm, 0°) < 0,25% R(1064nm, 0°) < 0,25% Rave(500nm - 1100nm, 0°) < 1,00% 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ - P		
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	[®] Edmund Optics[®]		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			⊕	TITLE 7mm Dia x 7mm FL, YAG-BBAR Coated, Plano-Convex Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING						
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN: mm	DWG NO 71299	SHEET SIZE A4	SHEET 1 OF 1