






f' : 50,808 $\pm$ 0,51

BACK FOCAL LENGTH (BFL): 44,084



LEFT SURFACE			MATERIAL	RIGHT SURFACE														
R 39,87 CX Øe 49,3 λ AR R(532nm, 0°) < 0,25% R(1064nm, 0°) < 0,25% Rave(500nm - 1100nm, 0°) < 1,00% 3/ 3 (0,5) λ=632,8 nm 4/ 1,27' 5/ 40 - 20 6/ - P			GLASS N-SF11 785/258 Nd: 1,785 Vd: 25,68	R ∞ PL Øe 49,3 λ AR R(532nm, 0°) < 0,25% R(1064nm, 0°) < 0,25% Rave(500nm - 1100nm, 0°) < 1,00% 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ - P														
PROTECTIVE CHAMFERS AS NEEDED <table><tr><td>ROHS: COMPLIANT</td><td>SCALE: NONE</td><td>λ = 587,6nm</td></tr></table> SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110			ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm	FIRST ANGLE PROJECTION  ALL DIMS IN: mm	 Edmund Optics® <table><tr><td>TITLE</td><td colspan="2">50,8mm Dia x 50,8079mm FL, YAG-BBAR Coated, Plano-Convex Lens</td></tr><tr><td>DWG NO</td><td>71341</td><td>SHEET SIZE A4</td></tr><tr><td colspan="2"></td><td>SHEET 1 OF 1</td></tr></table>			TITLE	50,8mm Dia x 50,8079mm FL, YAG-BBAR Coated, Plano-Convex Lens		DWG NO	71341	SHEET SIZE A4			SHEET 1 OF 1
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm																
TITLE	50,8mm Dia x 50,8079mm FL, YAG-BBAR Coated, Plano-Convex Lens																	
DWG NO	71341	SHEET SIZE A4																
		SHEET 1 OF 1																