

Laser Pulse Parameter Measurement



DA320-SI

Features:

- 1.Wavelength range:320-1100nm
- 2.Fixed gain low noise amplifier
- 3.Built-in 50 Ω load impedance
- 4.Equipped with ±12V stabilized voltage supply

SPECIFICATIONS

Model	DA320-SI
Wavelength Range	320-1100nm
Sensitive Area	75.4mm²(Φ9.8mm)
Material	Si
Rise Time	35ns
Bandwidth	DC -11MHz
NEP	2.67-71.7x10 ⁻¹⁴ W/Hz ^{1/2}
Operating Temperature	10-50℃

