

Laser Pulse Parameter Measurement



DA350-SI

Features:

- 1.Wavelength range:350-1100nm
- 2.Fixed gain low noise amplifier
- 3.Built-in 50 Ω load impedance
- 4.Equipped with ±12V stabilized voltage supply

SPECIFICATIONS

Model	DA350-SI
Wavelength Range	350-1100nm
Sensitive Area	13mm²(3.6*3.6mm)
Material	Si
Rise Time	10ns
Bandwidth	DC -12MHz
NEP	1.2x10 ⁻¹⁴ W/Hz ^{1/2}
Operating Temperature	10-50℃

