

Revision date: 12.04.2019 Revision No: 1,0

Telefax: +49 (0)6131 / 66 20 00

Print date: **26.04.2019**

Material Data Sheet

according to 29 CFR 1910.1200(g)

1. Identification

Product identifier

IRG26

Further trade names

IRG26 (amorphes Arsensulfid, Natriumselenid)
CAS No: 92128-37-5

Recommended use of the chemical and restrictions on use

Use of the substance/mixture

Glass. Reserved for industrial and professional use.

Post-processing by means of single diamond turning not without scrubber and conventional cold post-processing not without liquid coolant to absorb the resulting grinding dust.

Uses advised against

Do not use for private purposes (household).

Details of the supplier of the material data sheet

Company name: SCHOTT AG
Street: Hattenbergstr. 10
Place: D-55122 Mainz
Telephone: +49 (0)6131 / 66 0

Contact person: Dr. Kristian Eichgrün

e-mail: ehs-compliance.ao@schott.com

Internet: www.schott.com

Responsible Department: Qualitätsmanagement Advanced Optics

Telephone: +49 (0)61 31 / 66 21 55 Telefax: +49 (0)36 41 / 28 88 90 54

Emergency phone number: +49 61 31 / 66 2393 (Mo - Fr, 7 - 16 Uhr; MEZ; UTC+01)

2. Hazard(s) identification

Classification of the chemical

29 CFR Part 1910.1200

This substance is not classified as hazardous in accordance with Regulation 29 CFR 1910.1200(d).

Label elements

Additional advice on labelling

GHS label elements, including precautionary statements: none/none

Hazards not otherwise classified

In case of inhalation (particulates and dust):

Irritation to respiratory tract. A repeated, excessive dust exposure can cause pneumoconiosis.

3. Composition/information on ingredients

Substances

Chemical characterization

Glass, nonoxide, chemicals CAS No.: 92128-37-5 EC No.: 295-731-7

Sum formula: As40Se60



Revision date: 12.04.2019 Revision No: 1,0
Print date: 26.04.2019

Material Data Sheet

according to 29 CFR 1910.1200(g)

4. First-aid measures

Description of first aid measures

After inhalation

Provide fresh air. When in doubt or if symptoms are observed, get medical advice.

After contact with skin

particulates and dust: In case of skin reactions, consult a physician.

After contact with eyes

particulates and dust: Rinse immediately carefully and thoroughly with eye-bath or water. In case of eye irritation consult an ophthalmologist.

After ingestion

particulates and dust: Get medical advice/attention.

Most important symptoms and effects, both acute and delayed

No known symptoms to date.

Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Co-ordinate fire-fighting measures to the fire surroundings.

Specific hazards arising from the chemical

The product itself does not burn. In case of fire may be liberated: Metal oxide smoke, toxic

Special protective equipment and precautions for fire-fighters

Wear a self-contained breathing apparatus and chemical protective clothing. Full protection suit.

Additional information

Supress gases/vapours/mists with water spray jet. Collect contaminated fire extinguishing water separately. Do not allow entering drains or surface water.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Provide adequate ventilation. Avoid dust formation. Do not breathe dust. Avoid contact with skin, eyes and clothes. Use personal protection equipment.

Environmental precautions

Do not allow to enter into surface water or drains.

Methods and material for containment and cleaning up

Take up mechanically. Treat the recovered material as prescribed in the section on waste disposal.

Reference to other sections

Safe handling: see section 7

Personal protection equipment (PPE): see section 8

Disposal: see section 13

7. Handling and storage

Precautions for safe handling

Advice on safe handling

Provide adequate ventilation. Avoid dust formation. Do not breathe dust. Avoid contact with skin, eyes and clothes. Use personal protection equipment.



Revision date: 12.04.2019 Revision No:

1.0

Print date: **26.04.2019**

Material Data Sheet

according to 29 CFR 1910.1200(g)

Advice on protection against fire and explosion

No special fire protection measures are necessary.

Conditions for safe storage, including any incompatibilities

Requirements for storage rooms and vessels

Keep locked up. Store in a place accessible by authorized persons only. Provide adequate ventilation as well as local exhaustion at critical locations. Store in a dry place.

Hints on joint storage

Do not store together with: Strong acid, hydrofluoric acid, phosphoric and phosphorous acid, Alkali (lye), concentrated

Further information on storage conditions

Protect from moisture.

8. Exposure controls/personal protection

Control parameters

Exposure limits

CAS No.	Substance	ppm	mg/m³	f/cc	Category	Origin
-	Arsenic inorganic compounds, as As		0.01		TWA (8 h)	ACGIH-2018
7440-38-2	Arsenic, inorganic compounds (as As)	-	0.01		TWA (8 h)	PEL
-	Particulates not Otherwise regulated (PNOR) Total dust	1765 mp/m³			TWA (8 h)	PEL
7782-49-2	Selenium compounds (as Se)	-	0.2		TWA (8 h)	PEL
-	Selenium compounds, as Se		0.2		TWA (8 h)	ACGIH-2018
7782-49-2	Selenium	-	0.2		TWA (8 h)	REL
			0.2		TWA (8 h)	ACGIH-2018

Exposure controls





Appropriate engineering controls

Provide adequate ventilation as well as local exhaustion at critical locations. Technical measures and the application of suitable work processes have priority over personal protection equipment.

Protective and hygiene measures

Remove contaminated, saturated clothing immediately. Disposal of contaminated protective clothing separately, do not reuse. Draw up and observe skin protection programme. Wash hands and face before breaks and after work and take a shower if necessary. When using do not eat or drink.

Eye/face protection

Wear eye/face protection.

Hand protection

Wear suitable gloves. (cut-resistant)

Skin protection

Wear suitable protective clothing. Disposal of contaminated protective clothing separately, do not reuse.

Respiratory protection

In case of inadequate ventilation wear respiratory protection.



Revision date: 12.04.2019 Revision No: 1,0

Print date: **26.04.2019**

Material Data Sheet

according to 29 CFR 1910.1200(g)

Environmental exposure controls

Do not allow to enter into surface water or drains.

9. Physical and chemical properties

Information on basic physical and chemical properties

Physical state: solid

Color: colorless / coloured

Odor: odorless

Test method

pH-Value: 6,7 (on solid) OECD 122

Changes in the physical state

Initial boiling point and boiling range: not determined

glass transition temperature (Tg): 185 °C ISO 7884-8

Flash point: not applicable

Flammability

Solid: not applicable
Gas: not applicable

Explosive properties

The product is not: Explosive.

Lower explosion limits:

Upper explosion limits:

Ignition temperature:

not applicable
not applicable

Auto-ignition temperature

Solid: not applicable
Gas: not applicable
Decomposition temperature: 350 - 400 °C

Oxidizing properties

Not oxidising.

Vapor pressure: up to Tg no significant vapor pressure is to be

expected

Density (at 20 °C): 4,63 g/cm³ Water solubility: Immiscible

Solubility in other solvents

Not oxidising.

Partition coefficient:

Viscosity / dynamic:

Niscosity / kinematic:

Napor density:

Evaporation rate:

The substance is not soluble in water.

not applicable (solid)

not applicable (solid)

Other information

Odor threshold: not determined

10. Stability and reactivity



Revision date: 12.04.2019 Revision No: 1,0

Print date: 26.04.2019

Material Data Sheet

according to 29 CFR 1910.1200(g)

Reactivity

No hazardous reaction when handled and stored according to provisions.

Chemical stability

Stability: Stable

The product is stable under storage at normal ambient temperatures.

Crystallization > 300 °C

Degassing takes place from temperatures above: > 350 °C

Decompostion takes place from temperatures above: > 350 °C

Possibility of hazardous reactions

Hazardous reactions: May occur

Reacts with: Strong acid, hydrofluoric acid, phosphoric and phosphorous acid, Alkali (lye), concentrated

Conditions to avoid

Humidity

Temperature > point of degassing (Formation of: Metal oxide smoke, toxic)

Incompatible materials

Strong acid, hydrofluoric acid, phosphoric and phosphorous acid, Alkali (Iye), concentrated

Hazardous decomposition products

Metal oxide smoke, toxic (Temperature > point of degassing)

11. Toxicological information

Information on toxicological effects

Route(s) of Entry

dermal, Inhalation (particulates and dust), Eye contact (particulates and dust)

Acute toxicity

Based on available data, the classification criteria are not met.

The toxicological potential of glasses results from the bioavailability of individual components when used improperly. This is determined by the bioaccessibility test according to Fraunhofer. It is a leaching method of the material performed in 5 artificial body fluids.

Acute oral toxicity: no bioaccessibility detected

Acute dermal toxicity: no bioaccessibility detected

Acute inhalation toxicity: no hipaccessibility detected

Irritation and corrosivity

Based on available data, the classification criteria are not met.

Skin corrosion/irritation:

pH: 6,7 (OECD 122)

Result / evaluation: Not an irritant.

Serious eye damage/irritation:

pH: 6,7 (OECD 122)

Result / evaluation: Not an irritant.

Sensitizing effects

Based on available data, the classification criteria are not met.

Carcinogenic/mutagenic/toxic effects for reproduction

Based on available data, the classification criteria are not met.



Revision date: 12.04.2019 Revision No:

1.0

Print date: **26.04.2019**

Material Data Sheet

according to 29 CFR 1910.1200(g)

Specific target organ toxicity (STOT) - single exposure

Based on available data, the classification criteria are not met.

Specific target organ toxicity (STOT) - repeated exposure

Based on available data, the classification criteria are not met.

Carcinogenicity (OSHA): Arsenic compounds, inorganic is listed.

Carcinogenicity (IARC): Selenium (CAS 7782-49-2) is listed in group 3. Selenium compounds is listed in

group 3. Arsenic compounds, inorganic is listed in group 1.

Carcinogenicity (NTP): Arsenic compounds, inorganic is listed in group Known.

Aspiration hazard

Based on available data, the classification criteria are not met.

12. Ecological information

Ecotoxicity

The ecotoxicological effect of glasses is determined by the ecological accessability of hazardous substances that can be released under environmental conditions from the glass matrix. For characterization, the OECD29 test is used. In the evaluation, the leachable hazardous substance content, in relation to the total amount of the per se non-hazardous glass, is treated as a standard mixture proportion and classified accordingly.

Result / evaluation: no bioaccessibility detected

The product is not: Ecotoxic.

Persistence and degradability

The product has not been tested.

Bioaccumulative potential

The product has not been tested.

Mobility in soil

The product has not been tested.

Other adverse effects

No information available.

Further information

Avoid release to the environment.

13. Disposal considerations

Waste treatment methods

Advice on disposal

Do not allow to enter into surface water or drains. Neither the product nor the residues from the processing. Dispose of waste according to applicable legislation.

Contaminated packaging

Dispose of waste according to applicable legislation.

14. Transport information

US DOT 49 CFR 172.101

<u>Proper shipping name:</u> No dangerous good in sense of this transport regulation.

Marine transport (IMDG)

UN number:No dangerous good in sense of this transport regulation.UN proper shipping name:No dangerous good in sense of this transport regulation.Transport hazard class(es):No dangerous good in sense of this transport regulation.Packing group:No dangerous good in sense of this transport regulation.



Revision date: 12.04.2019 Revision No: 1,0

Print date: **26.04.2019**

Material Data Sheet

according to 29 CFR 1910.1200(g)

Air transport (ICAO-TI/IATA-DGR)

UN number:No dangerous good in sense of this transport regulation.UN proper shipping name:No dangerous good in sense of this transport regulation.Transport hazard class(es):No dangerous good in sense of this transport regulation.Packing group:No dangerous good in sense of this transport regulation.

Environmental hazards

ENVIRONMENTALLY HAZARDOUS: no

Special precautions for user

No information available.

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

not applicable

15. Regulatory information

U.S. Regulations

National Inventory TSCA

CAS No. 92128-37-5: Glass, nonoxide, chemicals: No.

National regulatory information

RA Section 302 Extremely hazardous substances:

Arsenic trioxide (1327-53-3): Reportable quantity = 1 lbs., Threshold planning quantity = 100/10,000 lbs.

RA Section 304 CERCLA:

Selenium (7782-49-2): Reportable quantity = 100 (45.4) lbs. (kg)

Arsenic trioxide (1327-53-3): Reportable quantity = 1 (0.454) lbs. (kg)

Selenium compounds (-): Reportable quantity = &

RA Section 313 Toxic release inventory:

Selenium (7782-49-2): De minimis limit = 1.0 %, Reportable threshold = Standard

Arsenic trioxide (1327-53-3): De minimis limit = 0.1 %, Reportable threshold = Standard

Selenium compounds (-): De minimis limit = 1.0 %, Reportable threshold = Standard

an Air Act Section 112(b):

Selenium (7782-49-2), Arsenic trioxide (1327-53-3), Selenium compounds (-)

State Regulations

Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65, State of California)

This product can not expose you to chemicals known to the State of California to cause cancer, birth defects or other reproductive harm.

Additional information

To follow: 29 CFR Part 1910.1018 (Inorganic arsenic)

16. Other information

Hazardous Materials Information Label (HMIS)

Health: 1
Flammability: 0
Physical Hazard: 0

NFPA Hazard Ratings

Health: 1
Flammability: 0
Reactivity: 0
Unique Hazard:





Revision date: 12.04.2019 Revision No: 1,0

Print date: **26.04.2019**

Material Data Sheet

according to 29 CFR 1910.1200(g)

Revision date: 12.04.2019

Revision No: 1,0

Abbreviations and acronyms

ADR: Accord européen sur le transport des marchandises dangereuses par Route

(European Agreement concerning the International Carriage of Dangerous Goods by Road)

CFR: Code of Federal Regulations DNEL: derived no-effect level DOT: Department of Transportation

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association IARC: International Agency for Research on Cancer

GHS: Globally Harmonized System of Classification and Labelling of Chemicals EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service LC50: Lethal concentration, 50%

LD50: Lethal dose, 50%

NFPA: National Fire Protection Association

NTP: National Toxicology Program

OSHA: Occupational Safety and Health Administration SARA: Superfund Amendments and Reauthorization Act

TSCA: Toxic Substances Control Act Tg: Glass transition temperature

Other data

The information is based on present level of our knowledge. It does not, however, give assurances of product properties and establishes no contract legal rights. The receiver of our product is singulary responsible for adhering to existing laws and regulations.