




f': 12 ± 0,12

BACK FOCAL LENGTH (BFL): 10



LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 6,2 CX Øe 7,2 (λ) AR R(532nm, 0°) < 0,25% R(1064nm, 0°) < 0,25% Rave(500nm - 1100nm, 0°) < 1,00% 3/ 3 (0,5) λ=632,8 nm 4/ 1,93' 5/ 40 - 20 6/ -			GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL Øe 7,2 (λ) AR R(532nm, 0°) < 0,25% R(1064nm, 0°) < 0,25% Rave(500nm - 1100nm, 0°) < 1,00% 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ -		
PROTECTIVE CHAMFERS AS NEEDED ROHS: COMPLIANT SCALE: NONE λ = 587,6nm SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110			FIRST ANGLE PROJECTION ALL DIMS IN: mm	Edmund Optics® TITLE 8mm Dia x 12mm FL, YAG-BBAR Coated, Plano-Convex Lens DWG NO 71334 SHEET SIZE A4 SHEET 1 OF 1		