



NOTES:
1. SUBSTRATE:
BOROFLOAT®

2. COATING (APPLY ACROSS CLEAR APERTURE)
S1: DIELECTRIC MIRROR (400 - 750nm)
R(avg) >99% @ 400 - 750nm @ 0 - 45° AOI
R(avg) >99% @ 400 - 750nm @ 0° AOI

S2: NONE




3. FINE GRIND SURFACE

4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	 Edmund Optics®			
SHAPE	PLANO	PLANO				
CLEAR APERTURE (%)	90	N/A				
SURFACE QUALITY	60 - 40	COMMERCIAL POLISH		TITLE	20mm Dia. 400 - 750nm Broadband λ/4 Mirror	
SURFACE FLATNESS	λ/4	N/A				
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED				
			ALL DIMS IN	mm	DWG NO	70670
					SHEET 3 OF 5	