




NOTES:

- 1. SUBSTRATE:
BOROFLOAT®
- 2. COATING PERFORMANCE (APPLY ACROSS COATING APERTURE)
T(AVG) <1.0% @ 400 - 480nm
T(AVG) >80% @ 525 - 555nm
T(AVG) <1.0% @ 590 - 720nm
T(ABS) <1.0% @ 425 - 455nm
T(ABS) >70% @ 530 - 550nm
T(ABS) <1.0% @ 620 - 690nm



3. FINE GROUND SURFACE

- 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	 Edmund Optics®			
SHAPE	PLANO	PLANO		TITLE	25mm Diameter, Green Dichroic Filter	
SURFACE QUALITY	80-50	80-50		DWG NO	52534	SHEET 1 OF 1
CLEAR APERTURE	≥85%	≥85%				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm		