





SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY





MOUNTING HOLE CENTERED ON OPTIC FACE

RUBBER PAD

UPTO 4.73mm [.186"] THICK x 85mm LONG OPTIC OR
UPTO 7.1mm [.28"] THICK x 80mm LONG OPTIC

M4 SOCKETHEAD SCREW
USES 3mm ALLEN WRENCH


SECTION B-B



61.80mm
[2.433"]

10.00mm
[.393"]

SECTION A-A



Edmund Optics®

TITLE	T-Mount Holder for any 60 x 85mm Plate Beamsplitter, 1/4-20		
DWG NO	65982	REV	000

Enable 3D View