

LOCKING SCREW  
M6 x 5.5[.217] DEEP

2X 32.00  
[1.260]

3X 24.00  
[.945]

2X 24.00  
[.945]

2X 32.00  
[1.260]

MICROMETER BASE



8X M2 x 5[.197] DEEP  
4X M3 x 5[.197] DEEP

SPECIFICATIONS SUBJECT TO CHANGE  
WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY  
DIMENSIONS ARE IN mm [INCHES]



Edmund Optics

TITLE	40mm CENTER DRIVE, METRIC EXTENDED MICROMETER STAGE		
DWG NO	66410	SHEET 1 OF 2	REV 000



SPECIFICATIONS SUBJECT TO CHANGE  
WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY  
DIMENSIONS ARE IN mm [INCHES]



Edmund Optics

TITLE	40mm CENTER DRIVE, METRIC EXTENDED MICROMETER STAGE			
DWG NO	66410	SHEET 2 OF 2	REV	000

Enable 3D View