



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy


TECHSPEC® ACHROMATIC LENSES



CHROMATIC FOCAL SHIFT

45213
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 367.7452 μm
DIFFRACTION LIMITED RANGE: 27.112 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM




TRANSVERSE RAY FAN PLOT

45213
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 200.000 \mu\text{m}$.
0.486 0.588 0.656

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

SURFACE: IMAGE



POLYCHROMATIC DIFFRACTION MTF

45213
TUE DEC 16 2008
DATA FOR 0.4000 TO 0.7000 μm .
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM