


TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy


TECHSPEC® ACHROMATIC LENSES



47689
TUE DEC 16 2008 UNITS ARE μm.
FIELD : 31.744
RMS RADIUS : 78.472
SCALE BAR : 200


EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

REFERENCE : CHIEF RAY



47689
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 59.0060 μm
DIFFRACTION LIMITED RANGE: 6.285 μm
PUPIL ZONE: 0.0000


EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



47689
TUE DEC 16 2008
MAXIMUM SCALE: ± 200.000 μm.
0.486 0.588 0.656

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

SURFACE: IMAGE



47689
TUE DEC 16 2008
DATA FOR 0.4250 TO 0.6750 μm.
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM