



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy


TECHSPEC® ACHROMATIC LENSES



CHROMATIC FOCAL SHIFT

49322
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 239.7807 μm
DIFFRACTION LIMITED RANGE: 5.999 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM




TRANSVERSE RAY FAN PLOT

49322
TUE DEC 16 2008
MAXIMUM SCALE: ± 500.000 μm.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



POLYCHROMATIC DIFFRACTION MTF

49322
TUE DEC 16 2008
DATA FOR 0.4000 TO 1.0000 μm.
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

EO Edmund
optics | worldwide

www.edmundoptics.com