



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES



49771
TUE DEC 16 2008 UNITS ARE μm.
FIELD :
RMS RADIUS : 209.851
GD RADIUS : 612.606
SCALE BAR : 2000


REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

49771
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 76.2277 μm
DIFFRACTION LIMITED RANGE: 3.782 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

CHROMATIC FOCAL SHIFT




TRANSVERSE RAY FAN PLOT

49771
TUE DEC 16 2008
MAXIMUM SCALE: ± 1000.000 μm.
0.486 0.588 0.656
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

49771
TUE DEC 16 2008
DATA FOR 0.4250 TO 0.6750 μm.
SURFACE: IMAGE

POLYCHROMATIC DIFFRACTION MTF



EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

EO Edmund
optics | worldwide

www.edmundoptics.com