TECHSPEC[®] ReflX[™] OBJECTIVES #89-726 • 30.56mm WD • 10X/0.22NA PROTECTED GOLD

Reflective Objectives are commonly used in applications requiring superior image quality or focusing performance over a broad spectral range. The schwarzschild-style objective exhibits near-diffraction limited performance over the full reflecting range of the chosen coating. By eliminating the problems of chromatic aberration and material absorption associated with standard microscope objectives, these components are ideal for applications requiring high throughput and excellent resolution in the UV or IR, including FTIR spectroscopy, ellipsometry, photolithography, and semiconductor inspection.

|--|

Style:	Infinity Corrected	
Magnification:	10X	
Numerical Aperture NA:	0.22	
Working Distance (mm):	30.56	
Focal Length FL (mm):	19.3	
Field of View, ¾" Sensor:	0.88 x 0.66mm	
Field of View, ½" Sensor:	0.64 x 0.48mm	
Transmitted Wavefront, RMS:	λ/10	
Obscuration (%):	27	
Entrance Pupil (mm):	8.4921 (Diameter)	



Figure 1: Dimensions of Objective.

Aperture Diameter (mm):	8.6	
Diameter of Small Mirror (mm):	8.9	
Reflection (%):	0.94	
Coating:	Protected Gold	
Coating Specification:	R _{avg} >97% @ 800 - 2000nm	R _{ovg} >94% @ 700 - 800nm
Mounting Threads:	RMS	
Туре:	Microscope Objective	
Wavelength Range (µm):	0.55 - 20	
Wavelength Range (nm):	550 - 20000	
Manufacturer:	EO	



Figure 2: Spectral Reflectance Curve.

