



NOTES:
1. RoHS: COMPLIANT

FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

Edmund Optics®

	VALUE
DESIGN WAVELENGTH DWL (nm)	266
INPUT DIAMETER	6.3mm (1/e ²)
WAVELENGTH RANGE(nm)	250 - 275



ALL DIMS IN mm

TITLE	266nm Flat Top Beam Shaper πShaper 6_6_266		
DWG NO	34255	SHEET 1 OF 1	