





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
CUT-ON WAVELENGTH	950nm
TRANSMISSION WAVELENGTH	985 - 2000nm
REJECTION WAVELENGTH	715 - 900nm
TRANSMISSION	>85
SURFACE QUALITY	40-20
COATING TYPE	TRADITIONAL COATED

EO[®] Edmund Optics[®]



ALL DIMS IN

mm

TITLE

M30.5 x 0.5, 950nm MOUNTED LONGPASS
FILTER

DWG NO

66695

SHEET
1 OF 1