





**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

| REV. A                  | VALUE                          |
|-------------------------|--------------------------------|
| CENTER WAVELENGTH (CWL) | 457 530 & 628 ± 2nm            |
| MINIMUM TRANSMISSION    | >90%                           |
| BLOCKING                | 250 - 1100nm                   |
| CONSTRUCTION            | MOUNTED IN BLACK ANODIZED RING |
| COATING TYPE            | HARD COATED                    |
| DURABILITY              | MIL-C-48497A                   |

THIRD ANGLE  
PROJECTION

ALL DIMS IN      mm

 **Edmund Optics®**

TITLE

Ø12.5mm, 457 530 & 628nm, TRI-BAND  
FILTER

DWG NO

87237

SHEET  
1 OF 1