





FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
CENTER WAVELENGTH (CWL)	464 542 & 639 ± 2nm
MINIMUM TRANSMISSION	>90%
BLOCKING	250 - 1100nm
CONSTRUCTION	MOUNTED IN BLACK ANODIZED RING
COATING TYPE	HARD COATED
DURABILITY	MIL-C-48497A

 **Edmund Optics®**



ALL DIMS IN

mm

TITLE

Ø25mm, 464 542 & 639nm, TRI-BAND FILTER

DWG NO

87246

SHEET  
1 OF 1