




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**




BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| REV. A | VALUE |
|-------------------------|--------------------------------|
| CENTER WAVELENGTH (CWL) | 440 521 607 & 700 ± 2nm |
| MINIMUM TRANSMISSION | >90% |
| BLOCKING | 250 - 1100nm |
| CONSTRUCTION | MOUNTED IN BLACK ANODIZED RING |
| COATING TYPE | HARD COATED |
| DURABILITY | MIL-C-48497A |

THIRD ANGLE
PROJECTION



ALL DIMS IN

mm

EO® **Edmund Optics**®

TITLE

Ø25mm, 440 521 607 & 700nm, QUAD-BAND FILTER

DWG NO

87247

SHEET
1 OF 1