





**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



IMAGING FILTER




| REV. A                     | VALUE                                   |
|----------------------------|-----------------------------------------|
| CENTER WAVELENGTH (CWL)    | 548 $\pm$ 2nm                           |
| FULL WIDTH HALF MAX (FWHM) | 290 $\pm$ 2nm                           |
| AVERAGE TRANSMISSION (%)   | $\geq 90$                               |
| BLOCKING                   | 200 - 1100                              |
| SURFACE QUALITY            | 80-50                                   |
| CONSTRUCTION               | MOUNTED IN BLACK ANODIZED ALUMINUM RING |
| COATING TYPE               | HARD COATED                             |
| DURABILITY                 | MIL-C-48497A, SECT. 3.4.1               |
| ENVIRONMENTAL              | MIL-STD-801F, SECT. 507.4               |

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO<sup>®</sup> Edmund Optics<sup>®</sup>**

THIRD ANGLE  
PROJECTION



TITLE

UV/IR CUT-OFF M46.0 X 0.75 IMAGING FILTER

ALL DIMS IN

mm

DWG NO

89800

SHEET  
1 OF 1