NOTES:

1. SUBSTRATE: FLOAT GLASS

2. ANTI REFLECTION SURFACE TREATMENT (APPLY ACROSS CLEAR APERTURE)


AOI: 0°


S1 & S2: Ravg ≤0.5% @ 425 - 700nm



4. ROHS COMPLIANT







FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

\$1	\$2
PLANO	PLANO
80-50	80-50
≥90%	≥90%
PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED
21	80-50 ≥90%

			Edmund Optics ®		
THIRD ANGLE - PROJECTION	$\phi \Box$	TITLE	Ø50.8mm x 3mm HIGH EFFICIENCY WIN	DOW	
ALL DIMS IN	mm	DWG NO	46100	SHEET 1 OF 1	