
NOTES:

1. SUBSTRATE:

FLOAT GLASS


 ANTI REFLECTION SURFACE TREATMENT (APPLY ACROSS CLEAR APERTURE) AOI: 0°
\$1 & \$2: Ravg ≤0.5% @ 425 - 700nm





FOR INFORMATION ONLY: DO NOT MANUFACTURE

PARTS TO THIS DRAWING



	S1	\$2				Eamuna Optic	S™
SHAPE	PLANO	PLANO		1			
SURFACE QUALITY	80-50	80-50			TITLE	50.8 x 50.8 x 1mm HIGH EFFICIENCY WINDOW	
CLEAR APERTURE	≥90%	≥90%					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	48925	1 OF 1