

NOTES:



1. SUBSTRATE: Float Glass
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: Protected Gold (700-10000nm)

R(AVG) >96% @ 700 - 2000nm

R(AVG) >96% @ 2000 - 10,000nm

S2: NONE
3. EDGES GROUND
4. RoHS COMPLIANT



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	<div><div>THIRD ANGLE PROJECTION</div><div></div></div>				
SHAPE	PLANO	PLANO					
SURFACE QUALITY	60-40	N/A	ALL DIMS IN	mm	TITLE	18mm Dia Protected Gold, 4-6λ Mirror	
SURFACE FLATNESS	4 - 6λ	N/A			DWG NO	45522	
CLEAR APERTURE	Ø 17.00	N/A					
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED					
					Edmund Optics®		
					SHEET 1 OF 1		