


NOTES:

1. SUBSTRATE: Float Glass
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: Protected Gold (700-10000nm)

R(AVG) >96% @ 700 - 2000nm
R(AVG) >96% @ 2000 - 10,000nm

S2: NONE
3. EDGES GROUND
4. RoHS COMPLIANT



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	<div><div><div>THIRD ANGLE PROJECTION</div></div><div>Edmund Optics®</div></div>			
SHAPE	PLANO	PLANO	TITLE6.35mm Dia Protected Gold, 4-6λ Mirror			
SURFACE QUALITY	60-40	N/A	ALL DIMS INmm	DWG NO45611	SHEET1 OF 1	
SURFACE FLATNESS	4 - 6λ	N/A				
CLEAR APERTURE	ϕ5.35	N/A				
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED				