





NOTES:

- 1. SUBSTRATE:
BOROFLOAT®
- 2. COATING SPECIFICATION:
S1: Enhanced Aluminum (250-700nm)
R(AVG) >89% @ 250 - 450nm
R(AVG) >85% @ 250 - 700nm
- 3. FINE GROUND SURFACE
- 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2			 Edmund Optics®		
SHAPE	PLANO	PLANO	THIRD ANGLE PROJECTION 	TITLE	15 x 15mm UV Enhanced Aluminum, λ/4 Mirror		
SURFACE QUALITY	60-40	COMMERCIAL POLISH					
CLEAR APERTURE	12.75 x 12.75	N/A					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	45726	SHEET 1 OF 1