




NOTES:

- 1. SUBSTRATE MATERIAL: Fused Silica
- 2. SURFACE S2 TO BE PARALLEL WITH S1 TO 30 arcsec
- 3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: UV Enhanced Aluminum  
R(avg) >89% @ 250 - 450nm  
R(avg) >85% @ 250 - 700nm  
S2: NONE

4. FINE GRIND SURFACE


5. RoHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY



REV. A	S1	S2	<div>THIRD ANGLE PROJECTION</div> 		TITLE	50mm Diameter UV Enhanced Aluminum Coated, λ/10 Mirror	
SURFACE QUALITY	20-10	COMMERCIAL POLISH			TITLE		
SURFACE FLATNESS	λ/10	NA	<div>ALL DIMS IN</div> <div>mm</div>		DWG NO	68319	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					