



NOTES:


1. SUBSTRATE: POLYMER FILM XP42-18
2. OPERATING TEMPERATURE: -40 TO +80 °C
3. WAVELENGTH RANGE: 400 - 700 nm
4. POLARIZATION: >99
5. TRANSMISSION (%):
SINGLE: 42
PARALLEL: 36
CROSSED: <0.004
6. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

 **Edmund Optics®**

THIRD ANGLE PROJECTION 		TITLE	200.0 X 200.0mm, 0.18mm, POLARIZING LAMINATED FILM	
ALL DIMS IN	mm	DWG NO	86181	SHEET 1 OF 1