## NOTES:

1. SUBSTRATE MATERIAL: FLOAT GLASS


2. ROHS COMPLIANT


3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: 25% R ±5% @ 550nm 75% T ±5% @ 550nm

S2: NONE







## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	\$1	\$2	
SHAPE	PLANO	PLANO	
SURFACE QUALITY	80-50	80-50	
SURFACE FLATNESS	4 - 6λ	4 - 6λ	
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	

THIRD ANGLE PROJECTION	$\phi \Leftrightarrow$	TITLE
ALL DIMS IN	mm	DWG NO

Edmund Optics®
50 x 50mm 25 R/75 T PLATE BEAMSPLITTER

50 x 50mm, 25 R/75 T, PLATE BEAMSPLITTER

DIMS IN	mm	DWG NO	43818	SHEET 1 OF 1
				1 01 1