



NOTES:

1. SUBSTRATE MATERIAL:
Fused Silica
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: Protected Silver
R(avg) >98% @ 450 - 2000nm
R(avg) >98% @ 2000 - 10,000nm
S2: NONE

3.

FINE GROUND SURFACE
4. PARALLELISM: 30 ARCSEC
5. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	<div><div><div>EO[®]</div><div>Edmund Optics[®]</div></div><div><div>TITLE</div><div>30mm Square Silver Coated, λ/10 Mirror</div></div><div><div>DWG NO</div><div>84442</div></div><div><div>SHEET</div><div>1 OF 1</div></div></div>
SHAPE	PLANO	PLANO	<div><div>THIRD ANGLE PROJECTION</div><div><div>ALL DIMS IN</div><div>mm</div></div></div>
SURFACE QUALITY	20-10	N/A	
SURFACE FLATNESS	λ/10	COMMERICAL POLISH	
CLEAR APERTURE	90%	N/A	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	