



NOTES:

- 1. COATING (APPLY ACROSS COATING APERTURE)  
T(AVG): >80% FROM 400 - 525  
CUT-OFF WAVELENGTH: 550nm ± 3%  
BLOCKING RANGE: 575 - 675nm
- 2. RoHS: COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® Edmund Optics®

	S1	S2	THIRD ANGLE PROJECTION		TITLE	550nm, 12.5mm Square, OD 2 Ultra-Thin Shortpass Filter	
SHAPE	PLANO	PLANO					
CLEAR APERTURE	11.25 x 11.25	11.25 x 11.25	ALL DIMS IN		DWG NO	35893	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					
			mm				SHEET 1 OF 1