




NOTES:

- 1. SUBSTRATE MATERIAL:
FLOAT GLASS
- 2. COATING (APFLOW ACROSS CLEAR APERTURE):
S1: ALUMINUM
S2: NONE
- 3. BLAZE ANGLE: 6.5°
NOMINAL BLAZE WAVELENGTH: 760nm
GROOVE DENSITY: 300 GROOVES/mm

- 4. EDGES GROUND
- 5. RoHS COMPLIANT




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® **Edmund Optics®**

	S1	S2
SHAPE	PLANO	PLANO
CLEAR APERTURE	22.5 x 22.5	22.5 x 22.5

THIRD ANGLE PROJECTION 		TITLE	Richardson Gratings™ 300 Grooves, 25 x 25mm, 760nm, Plane Ruled Reflection Grating	
ALL DIMS IN	mm	DWG NO	37129	SHEET 1 OF 1