



NOTES:
1. RoHS: COMPLIANT

FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

	VALUE
DESIGN WAVELENGTH DWL (nm)	1550
INPUT DIAMETER	6.4 - 6.5mm (1/e ²)
WAVELENGTH RANGE(nm)	1500-1600



ALL DIMS IN mm

TITLE	1550nm Flat Top Beam Shaper πShaper 6_6_1550
DWG NO	37700
SHEET	1 OF 1