





NOTES:


1. SUBSTRATE MATERIAL:
N-BK7
2. COATING:
- S1, S2, & S3: SILVER WITH PROTECTED OVERCOAT
R(ABS) > 97% FROM 400 - 2500nm @ 0° AOI
R(AVG) > 98% FROM 400 - 2500nm @ 0° AOI
3. RAY DEVIATION: 180°
4. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	S3
SHAPE	PLANO	PLANO	PLANO
SURFACE QUALITY	60-40	60-40	60-40
WAVELENGTH RANGE (nm)	500 - 10000	500 - 10000	500 - 10000
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	PROTECTED AS NEEDED

**Edmund Optics®**

THIRD ANGLE PROJECTION

ALL DIMS IN mm

TITLE

12.7mm Mounted Corner Cube Retroreflector

DWG NO

45203

SHEET 1 OF 1