

NOTES:

- 1. SUBSTRATE MATERIAL: FLOAT GLASS
- 2. COATING (APPLY ACROSS CLEAR APERTURE): \$1: BARE ALUMINUM \$2: NONE
- 3. WAVELENGTH RANGE: 250-400nm ABSOLUTE DIFFRACTION EFFICIENCY: 45-65% GROOVE DENSITY: 3600 grooves/mm



5. Rohs Compliant





SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

	\$1	\$2			
SHAPE	PLANO	PLANO			
CLEAR APERTURE	45.0 x 45.0	45.0 x 45.0			

	Edmund	Optics®
--	--------	---------

THIRD ANGLE PROJECTION	$\phi \lhd$	TITLE	GRATING HOLO 3600GR UV 50 X 5	0
ALL DIMS IN	mm	DWG NO	48469	SHEET 1 OF 1

