



NOTES:


- 1. COATING:
ALL SURFACES EXCEPT S1: Spectral Black™
- 2. ABSORBANCE: 99.9%
- 3. ABRASION RESISTANCE: Moderate
- 4. HUMIDITY RESISTANCE: MIL-C-48497A
- 5. OPERATING TEMPERATURE(°C) : -50 to 150
- 6. WAVELENGTH RANGE: 0.3 - 14µm



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO® **Edmund Optics®**

THIRD ANGLE PROJECTION 		TITLE	25mm Dia. Adhesive, Spectral Black Panel	
ALL DIMS IN	mm	DWG NO	37834	SHEET 1 OF 1