
NOTES:


- 1. SUBSTRATE: BOROFLOAT ®
- 2. COATING (APPLY ACROSS CLEAR APERTURE): S1 & S2: R(AVG) <1.0% @ 700 1150nm



FINE GRIND SURFACE

4. ROHS COMPLIANT





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2			
SHAPE	PLANO	PLANO			
SURFACE FLATNESS	4 - 6λ	4 - 6λ			
SURFACE QUALITY	80-50	80-50			
CLEAR APERTURE	22.50 x 22.50	22.50 x 22.50			
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED			

				Edmund Optic	S®
	THIRD ANGLE _ PROJECTION	$\phi \Box$	TITLE	25 x 25 x 3.3mm THICKNESS, NIR COA BOROFLOAT® WINDOW	TED,
)	ALL DIMS IN	mm	DWG NO	12191	SHEE 1 OF

