




NOTES:

- 1. COATING:
S1: SPECTRAL BLACK™
THICKNESS (µm) 3-7
- 2. ABSORBANCE: 99.9 (0 - 10° AOI)%
- 3. ABRASION RESISTANCE: MODERATE
- 4. HUMIDITY RESISTANCE: MIL-C-48497A
- 5. OPERATING TEMPERATURE (°C): -40 to 121
- 6. WAVELENGTH RANGE: 0.3 - 14



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

 Edmund Optics®			
THIRD ANGLE PROJECTION 		TITLE	Spectral Black Adhesive Foil Sheet 200 x 600mm
ALL DIMS IN	mm	DWG NO	88244
			SHEET 1 OF 1