



NOTES:


- 1. COATING:
S1: METAL VELVET™
THICKNESS (µm) 5-8
- 2. ABSORBANCE: 99.9 (0 - 10° AOI)%
- 3. ABRASION RESISTANCE: LIGHT, DO NOT TOUCH
- 4. HUMIDITY RESISTANCE: MIL-C-48497A
- 5. OPERATING TEMPERATURE (°C): -196 to 350
- 6. WAVELENGTH RANGE: 0.3 - 14



DETAIL A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

 Edmund Optics®			
THIRD ANGLE PROJECTION 		TITLE	Metal Velvet No Adhesive Foil Sheet 200 x 600mm
ALL DIMS IN	mm	DWG NO	12684
			SHEET 1 OF 1