



NOTES:

1. SUBSTRATE:  
N-BK7
2. COATING (APPLY ACROSS COATING APERTURE)  
NONE
3. SURFACE QUALITY: 60-40
4. WAVELENGTH RANGE: 350 - 2200 nm




SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

**EO**® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	75mm Diameter x 3mm Thickness, N-BK7 Glass Dome	
ALL DIMS IN	mm	DWG NO	64498	SHEET 1 OF 1