






- NOTES:
- 1. MATERIAL: FLOAT GLASS
 - 2. COATING:
S1 INCONEL
S2: LINEARLY VARIABLE OPTICAL DENSITY FROM 0.04 - 3.0
 - 3. EDGES: CUT
 - 4. WAVELENGTH RANGE: 400 - 700nm
 - 5. DENSITY NEUTRALITY $\pm 5\%$ OF OPTICAL DENSITY
 - 6. RoHS: COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] Edmund Optics[®]

| | | | | | | | |
|-------|----------------------|----------------------|--|----|--------|--|--------------|
| | S1 | S2 | THIRD ANGLE PROJECTION  | | TITLE | OD 0.04 -3.0, 76.2 x 25.4mm, CONTINUOUSLY VARIABLE ND FILTER | |
| SHAPE | PLANO | PLANO | ALL DIMS IN | mm | DWG NO | 64382 | SHEET 1 OF 1 |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED | | | | | |