NOTES:


MATERIAL:


HOUSING: STAINLESS STEEL LENS: D-ZK3


2. COATING (APPLY ACROSS CLEAR APERTURE) R(AVG) <0.4% @ 1050 - 1600nm

3. CLEAR APERTURE: 5.50 mm

4. RoHS: COMPLIANT







SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

Edmund Optics®

THIRD ANGLE PROJECTION TITLE 1064nm Alignment, 0.25 NA Fiber Collimator w/ SMA Connector

ALL DIMS IN mm DWG NO 64768 SHEET 1 OF 1

