




NOTES:

1. MATERIAL:  
HOUSING: STAINLESS STEEL  
LENS: D-ZK3
2. COATING (APPLY ACROSS CLEAR APERTURE)  
R(AVG) <0.4% @ 600 - 1050nm
3. CLEAR APERTURE: 5.50 mm
4. RoHS: COMPLIANT



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® Edmund Optics®

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

THIRD ANGLE PROJECTION		TITLE	633nm Alignment, 0.25 NA Fiber Collimator w/ SMA Connector	
ALL DIMS IN	mm	DWG NO	67725	SHEET 1 OF 1