
NOTES:


- 1. MATERIAL:
 HOUSING: STAINLESS STEEL
 LENS: D-ZLaF52LA
- 2. COATING (APPLY ACROSS COATING APERTURE) BBAR (600-1050nm) Rabs <1.0% @ 600 - 1050nm

3. CLEAR APERTURE: 5.07 mm

4. RoHS: COMPLIANT







SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

Edmund Optics®

THIRD ANGLE PROJECTION		TITLE	633nm Alignment, 0.55 NA Fiber Collimator w/ FC/APC Connector	
ALL DIMS IN	mm	DWG NO	13552	SHEET 1 OF 1

